

Product Specification

Small Batch Sieving

200-S

A 200mm diameter vibratory sieve designed to sit directly on top of a container.

A circular frame supports the sieve so that ingredients can be tipped into the top and check sieved into a container below.

The Sievmaster 200-S can be used for straining liquids as well as dry ingredients. Different mesh screens for coarse, medium & fine/liquid applications are available.



sm sievmaster
by farleygreene

Features & Benefits

- Easy-Clean hygienic design, no crevices
- Conforms to CE, UKCA, FDA, EC 1935/2004 and ANIA regulations
- No tool, quick change screens
- Wet or dry applications
- 0.05 kW (0.1 HP) vibratory motor
- Dust and waterproof to at least IP65
- Open top hopper for ease of dispensing
- All stainless steel body and contact parts
- Low maintenance/running costs – tool free disassembly & minimal servicing

Industries:



Food & Drink



Pharma



Chemical



Additive

Product Options*

Top Dust Cover - removable top cover with gasket and clamp.



Top Cone Meshed - ET5145 adhesive.



Bench Mounting Kit - allows the sieve to be freestanding.



Collection Bin - wheels available.



*More options available on request

Typical Materials

- Most food, beverage & chemical powders and granular products
- Liquid separation


Finishes available

- Internal Dull Polish to <0.8 Ra

Certified Technology



THIRD ANGLE PROJECTION




SM 200-S ARTISAN SIEVE



| DIMENSION | SM200-S (mm) |
|-----------|--------------|
| A | 565 |
| B | 300 |
| C | 250 |
| D | 150 |

Screen diameter = 200mm
Bench mount legs give outlet height @ 355mm from ground



| ELECTRICAL | SM200-S |
|------------|------------|
| Voltage | 110 / 240 |
| Frequency | 50 / 60 hz |
| Power | 45 w |
| Phase | 1 |
| ATEX | No |